

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224735

Luminaire Tested: **LSSQ2B15FL409035D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15FL409035D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1149.3 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224735

CATALOG NUMBER: LSSQ2B15FL409035D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224735

CATALOG NUMBER: LSSQ2B15FL409035D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1040489
5°	1021523
10°	908061
15°	714159
20°	475231
25°	272845
30°	137803
35°	64829
40°	26091
45°	12928
50°	7111
55°	4997
60°	4571
65°	2658
70°	3284
75°	2245
80°	3346
85°	0



TEST NUMBER: P224735

CATALOG NUMBER: LSSQ2B15FL409035D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.6	20.9
10°-20°	482.4	42.0
20°-30°	300.1	26.1
30°-40°	92.3	8.0
40°-50°	20.3	1.8
50°-60°	7.2	0.6
60°-70°	3.6	0.3
70°-80°	2.1	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.2	89.0
0°-40°	1115.4	97.1
0°-60°	1142.9	99.4
0°-90°	1149.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1149.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2686	
5°	2627	241
15°	1781	482
25°	638	300
35°	137	92
45°	24	20
55°	7	7
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224735

CATALOG NUMBER: LSSQ2B15FL409035D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2686.2
2.5°	2674.4
5°	2627.2
7.5°	2507.8
10°	2308.7
12.5°	2069.9
15°	1780.9
17.5°	1465.4
20°	1152.9
22.5°	874.3
25°	638.4
27.5°	449.7
30°	308.1
32.5°	207.9
35°	137.1
37.5°	82.6
40°	51.6
42.5°	35.4
45°	23.6
47.5°	16.2
50°	11.8
52.5°	10.3
55°	7.4
57.5°	5.9
60°	5.9
62.5°	4.4
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)