

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983502

Luminaire Tested: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B770UB2750-4F0-XX-W2A-1_3500K
Description: Define 5 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2721.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983502

CATALOG NUMBER: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983502

CATALOG NUMBER: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983502

CATALOG NUMBER: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	64.8	2.4
100°-110°	192.5	7.1
110°-120°	326.5	12.0
120°-130°	429.8	15.8
130°-140°	481.6	17.7
140°-150°	472.0	17.3
150°-160°	396.5	14.6
160°-170°	263.6	9.7
170°-180°	92.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	583.8	21.5
90°-150°	1967.2	72.3
90°-180°	2720.0	100.0
0°-180°	2721.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	3
95°	49	51	58	64	65	52
105°	173	177	181	186	188	184
115°	327	330	331	331	330	323
125°	477	482	482	481	480	427
135°	620	625	626	626	623	478
145°	752	754	757	757	754	470
155°	860	860	861	864	860	396
165°	935	934	934	937	933	264
175°	972	969	969	974	968	92
180°	974	974	974	974	974	

TEST NUMBER: P983502

CATALOG NUMBER: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.8	12.1	15.9	18.2
92.5°	22.7	26.5	33.4	38.7	40.2
95°	49.3	50.8	58.4	63.7	65.2
97.5°	75.8	76.6	87.2	91.8	92.5
100°	106.2	106.2	116.0	122.8	124.4
102.5°	138.8	142.6	146.4	153.9	156.2
105°	172.9	176.7	181.2	185.8	188.1
107.5°	210.0	213.8	217.6	219.9	219.9
110°	248.7	252.5	254.8	257.1	256.3

TEST NUMBER: P983502

CATALOG NUMBER: S125IW-B770UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	289.7	292.7	293.5	291.9
115°	326.8	329.9	331.4	330.6	329.9
117.5°	366.3	367.0	368.5	369.3	366.3
120°	402.7	406.4	407.2	407.2	404.2
122.5°	442.1	442.8	445.1	444.4	442.1
125°	477.0	481.5	482.3	480.8	480.0
127.5°	515.6	517.9	518.7	517.9	516.4
130°	549.8	553.6	555.1	554.3	552.8
132.5°	583.9	590.7	590.0	589.2	586.9
135°	620.3	624.8	625.6	625.6	622.6
137.5°	654.4	659.0	660.5	661.2	657.4
140°	687.0	690.8	693.1	694.6	690.8
142.5°	719.6	722.7	725.7	726.4	722.7
145°	751.5	754.5	756.8	756.8	754.5
147.5°	781.0	783.3	784.8	787.1	781.0
150°	810.6	809.9	812.9	812.9	811.4
152.5°	834.9	836.4	837.2	839.4	836.4
155°	859.9	859.9	860.7	863.7	859.9
157.5°	882.7	881.1	881.9	884.9	879.6
160°	902.4	900.1	900.8	903.9	900.1
162.5°	919.8	918.3	918.3	922.1	917.5
165°	935.0	933.5	934.2	937.2	932.7
167.5°	948.6	945.6	945.6	950.1	945.6
170°	959.2	956.2	956.2	960.8	955.4
172.5°	966.8	963.8	963.8	968.3	963.8
175°	972.1	969.1	969.1	973.6	968.3
177.5°	975.9	972.9	972.1	976.7	971.4
180°	974.4	974.4	974.4	974.4	974.4

(END OF REPORT)