

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15FL409035D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409035D010 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1160.1 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBD*LI

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96						
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91						
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87						
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83						
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79						
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76						
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73						
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70						
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67						
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1112845
5°	1069387
10°	930913
15°	726951
20°	483434
25°	276820
30°	137625
35°	63269
40°	25383
45°	11613
50°	5363
55°	3039
60°	1704
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.3	21.6
10°-20°	491.6	42.4
20°-30°	304.2	26.2
30°-40°	91.0	7.8
40°-50°	18.3	1.6
50°-60°	4.4	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.1	90.2
0°-40°	1137.1	98.0
0°-60°	1159.8	100.0
0°-90°	1160.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2873	
5°	2750	250
15°	1813	492
25°	648	304
35°	134	91
45°	21	18
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2873.0
1°	2857.4
2°	2842.9
3°	2813.9
4°	2787.1
5°	2750.3
6°	2700.2
7°	2636.6
8°	2555.2
9°	2462.7
10°	2366.8
11°	2267.6
12°	2161.7
13°	2051.3
14°	1933.2
15°	1812.8
17.5°	1495.0
20°	1172.8
22.5°	887.4
25°	647.7
27.5°	454.9
30°	307.7
32.5°	202.9
35°	133.8
37.5°	83.6
40°	50.2
42.5°	32.3
45°	21.2
47.5°	13.4
50°	8.9
52.5°	6.7
55°	4.5
57.5°	3.3
60°	2.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)