

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225401

Luminaire Tested: **LSSQWM2B15FL409035D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409035D010 2LBDC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1145.7 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225401

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225401

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	103	100		108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	86	82		88	85	82			87	84	81			79
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			76
7	91	83	78	75		90	83	78	75		81	77	74			80	77	74			72
8	87	80	75	72		86	79	75	71		78	74	71			77	74	71			69
9	84	77	72	69		83	76	72	68		75	71	68			74	71	68			67
10	82	74	69	66		81	73	69	66		73	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1036615
5°	1018606
10°	908690
15°	718249
20°	478900
25°	277846
30°	139056
35°	65397
40°	25586
45°	11394
50°	5363
55°	3039
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225401

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.1	21.0
10°-20°	484.8	42.3
20°-30°	305.0	26.6
30°-40°	93.2	8.1
40°-50°	18.3	1.6
50°-60°	4.1	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1029.9	89.9
0°-40°	1123.1	98.0
0°-60°	1145.5	100.0
0°-90°	1145.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1145.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2676	
5°	2620	240
15°	1791	485
25°	650	305
35°	138	93
45°	21	18
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225401

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2676.2
2.5°	2670.3
5°	2619.7
7.5°	2500.7
10°	2310.3
12.5°	2072.2
15°	1791.1
17.5°	1478.7
20°	1161.8
22.5°	891.1
25°	650.1
27.5°	458.2
30°	310.9
32.5°	209.8
35°	138.3
37.5°	84.8
40°	50.6
42.5°	32.7
45°	20.8
47.5°	13.4
50°	8.9
52.5°	6.0
55°	4.5
57.5°	3.0
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)