

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225463

Luminaire Tested: **LSSQWM2B15FL409035D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409035D010 2LBDLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1056.0 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225463

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225463

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	95	92		103	98	94	91		96	92	90		93	91	88		91	89	87
4	101	94	90	86		99	93	89	86		91	87	85		89	86	84		88	85	83
5	97	90	85	81		95	89	84	81		87	83	80		85	82	79		84	81	79
6	93	85	80	77		92	85	80	76		83	79	76		82	78	75		81	77	75
7	89	81	76	73		88	81	76	73		80	75	72		79	75	72		78	74	72
8	86	78	73	69		85	77	73	69		76	72	69		75	72	69		75	71	68
9	83	75	70	66		82	74	69	66		73	69	66		72	69	66		72	68	65
10	80	72	67	63		79	71	66	63		70	66	63		70	66	63		69	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	918242
5°	885356
10°	778658
15°	610337
20°	422716
25°	260451
30°	144915
35°	77313
40°	38328
45°	19556
50°	10726
55°	7023
60°	3486
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225463

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	19.7
10°-20°	415.7	39.4
20°-30°	284.0	26.9
30°-40°	108.3	10.3
40°-50°	30.1	2.8
50°-60°	9.4	0.9
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.4	85.9
0°-40°	1015.7	96.2
0°-60°	1055.1	99.9
0°-90°	1056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2371	
5°	2277	208
15°	1522	416
25°	609	284
35°	164	108
45°	36	30
55°	10	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225463

CATALOG NUMBER: LSSQWM2B15FL409035D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2370.6
2.5°	2345.4
5°	2277.0
7.5°	2149.2
10°	1979.7
12.5°	1764.2
15°	1522.0
17.5°	1273.8
20°	1025.5
22.5°	805.6
25°	609.4
27.5°	447.4
30°	324.0
32.5°	230.4
35°	163.5
37.5°	114.4
40°	75.8
42.5°	50.5
45°	35.7
47.5°	25.3
50°	17.8
52.5°	13.4
55°	10.4
57.5°	7.4
60°	4.5
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)