

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983476

Luminaire Tested: S125IW-B1560UB50-4F0-XX-W2A-1

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1560UB50-4F0-XX-W2A-1
Description: Define 5 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5280.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983476

CATALOG NUMBER: S125IW-B1560UB50-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P983476

CATALOG NUMBER: S125IW-B1560UB50-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983476

CATALOG NUMBER: S125IW-B1560UB50-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.9	0.1
90°-100°	125.7	2.4
100°-110°	373.5	7.1
110°-120°	633.5	12.0
120°-130°	834.0	15.8
130°-140°	934.5	17.7
140°-150°	916.0	17.3
150°-160°	769.4	14.6
160°-170°	511.5	9.7
170°-180°	179.0	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.9	0.1
90°-120°	1132.7	21.5
90°-150°	3817.2	72.3
90°-180°	5277.0	99.9
0°-180°	5280.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	13	24	31	35	6
95°	96	99	113	124	126	100
105°	336	343	352	360	365	358
115°	634	640	643	642	640	627
125°	926	934	936	933	931	829
135°	1204	1212	1214	1214	1208	928
145°	1458	1464	1468	1468	1464	912
155°	1669	1669	1670	1676	1669	769
165°	1814	1811	1813	1819	1810	512
175°	1886	1880	1880	1889	1879	179
180°	1891	1891	1891	1891	1891	

TEST NUMBER: P983476

CATALOG NUMBER: S125IW-B1560UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	13.2	23.5	30.9	35.3
92.5°	44.1	51.5	64.7	75.0	78.0
95°	95.6	98.6	113.3	123.6	126.5
97.5°	147.1	148.6	169.2	178.0	179.5
100°	206.0	206.0	225.1	238.4	241.3
102.5°	269.3	276.6	284.0	298.7	303.1
105°	335.5	342.8	351.7	360.5	364.9
107.5°	407.6	414.9	422.3	426.7	426.7
110°	482.6	490.0	494.4	498.8	497.3

TEST NUMBER: P983476

CATALOG NUMBER: S125IW-B1560UB50-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	559.1	562.1	568.0	569.4	566.5
115°	634.2	640.1	643.0	641.5	640.1
117.5°	710.7	712.2	715.1	716.6	710.7
120°	781.3	788.7	790.2	790.2	784.3
122.5°	857.8	859.3	863.7	862.3	857.8
125°	925.5	934.4	935.8	932.9	931.4
127.5°	1000.6	1005.0	1006.5	1005.0	1002.0
130°	1066.8	1074.1	1077.1	1075.6	1072.7
132.5°	1133.0	1146.2	1144.8	1143.3	1138.9
135°	1203.6	1212.5	1213.9	1213.9	1208.0
137.5°	1269.8	1278.7	1281.6	1283.1	1275.7
140°	1333.1	1340.5	1344.9	1347.8	1340.5
142.5°	1396.4	1402.3	1408.2	1409.6	1402.3
145°	1458.2	1464.1	1468.5	1468.5	1464.1
147.5°	1515.6	1520.0	1522.9	1527.4	1515.6
150°	1573.0	1571.5	1577.4	1577.4	1574.4
152.5°	1620.1	1623.0	1624.5	1628.9	1623.0
155°	1668.6	1668.6	1670.1	1676.0	1668.6
157.5°	1712.8	1709.8	1711.3	1717.2	1706.9
160°	1751.0	1746.6	1748.1	1754.0	1746.6
162.5°	1784.9	1781.9	1781.9	1789.3	1780.4
165°	1814.3	1811.3	1812.8	1818.7	1809.9
167.5°	1840.8	1834.9	1834.9	1843.7	1834.9
170°	1861.4	1855.5	1855.5	1864.3	1854.0
172.5°	1876.1	1870.2	1870.2	1879.0	1870.2
175°	1886.4	1880.5	1880.5	1889.3	1879.0
177.5°	1893.7	1887.9	1886.4	1895.2	1884.9
180°	1890.8	1890.8	1890.8	1890.8	1890.8

(END OF REPORT)