

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983492

Luminaire Tested: S125IW-B470UB35-4F0-XX-W2A-1

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB35-4F0-XX-W2A-1
Description: Define 5 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1651.0 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983492

CATALOG NUMBER: S125IW-B470UB35-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P983492

CATALOG NUMBER: S125IW-B470UB35-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983492

CATALOG NUMBER: S125IW-B470UB35-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.1
90°-100°	39.3	2.4
100°-110°	116.8	7.1
110°-120°	198.1	12.0
120°-130°	260.8	15.8
130°-140°	292.2	17.7
140°-150°	286.4	17.3
150°-160°	240.6	14.6
160°-170°	159.9	9.7
170°-180°	56.0	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.1
90°-120°	354.2	21.5
90°-150°	1193.6	72.3
90°-180°	1650.0	99.9
0°-180°	1651.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	10	11	2
95°	30	31	35	39	40	31
105°	105	107	110	113	114	112
115°	198	200	201	201	200	196
125°	289	292	293	292	291	259
135°	376	379	380	380	378	290
145°	456	458	459	459	458	285
155°	522	522	522	524	522	240
165°	567	566	567	569	566	160
175°	590	588	588	591	588	56
180°	591	591	591	591	591	

TEST NUMBER: P983492

CATALOG NUMBER: S125IW-B470UB35-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	4.1	7.4	9.7	11.0
92.5°	13.8	16.1	20.2	23.5	24.4
95°	29.9	30.8	35.4	38.6	39.6
97.5°	46.0	46.5	52.9	55.7	56.1
100°	64.4	64.4	70.4	74.5	75.5
102.5°	84.2	86.5	88.8	93.4	94.8
105°	104.9	107.2	110.0	112.7	114.1
107.5°	127.4	129.7	132.0	133.4	133.4
110°	150.9	153.2	154.6	156.0	155.5

TEST NUMBER: P983492

CATALOG NUMBER: S125IW-B470UB35-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	175.8	177.6	178.1	177.1
115°	198.3	200.1	201.1	200.6	200.1
117.5°	222.2	222.7	223.6	224.1	222.2
120°	244.3	246.6	247.1	247.1	245.2
122.5°	268.2	268.7	270.1	269.6	268.2
125°	289.4	292.2	292.6	291.7	291.2
127.5°	312.9	314.2	314.7	314.2	313.3
130°	333.6	335.9	336.8	336.3	335.4
132.5°	354.3	358.4	358.0	357.5	356.1
135°	376.4	379.1	379.6	379.6	377.7
137.5°	397.1	399.8	400.7	401.2	398.9
140°	416.9	419.2	420.5	421.5	419.2
142.5°	436.6	438.5	440.3	440.8	438.5
145°	456.0	457.8	459.2	459.2	457.8
147.5°	473.9	475.3	476.2	477.6	473.9
150°	491.8	491.4	493.2	493.2	492.3
152.5°	506.6	507.5	508.0	509.3	507.5
155°	521.8	521.8	522.2	524.1	521.8
157.5°	535.6	534.6	535.1	536.9	533.7
160°	547.5	546.1	546.6	548.4	546.1
162.5°	558.1	557.2	557.2	559.5	556.7
165°	567.3	566.4	566.8	568.7	565.9
167.5°	575.6	573.7	573.7	576.5	573.7
170°	582.0	580.2	580.2	582.9	579.7
172.5°	586.6	584.8	584.8	587.6	584.8
175°	589.9	588.0	588.0	590.8	587.6
177.5°	592.2	590.3	589.9	592.6	589.4
180°	591.2	591.2	591.2	591.2	591.2

(END OF REPORT)