

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224695

Luminaire Tested: **LSR2WM2B20FL408027D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408027D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1691.0 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224695

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224695

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	86	82	78	93	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1530869
5°	1503005
10°	1336074
15°	1050807
20°	699223
25°	401446
30°	202792
35°	95376
40°	38378
45°	19008
50°	10485
55°	7293
60°	6740
65°	3941
70°	4870
75°	3292
80°	4907
85°	0



TEST NUMBER: P224695

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.0	20.9
10°-20°	709.8	42.0
20°-30°	441.6	26.1
30°-40°	135.8	8.0
40°-50°	29.9	1.8
50°-60°	10.6	0.6
60°-70°	5.3	0.3
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1505.4	89.0
0°-40°	1641.2	97.1
0°-60°	1681.7	99.4
0°-90°	1691.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1691.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3952	
5°	3866	354
15°	2620	710
25°	939	442
35°	202	136
45°	35	30
55°	11	11
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224695

CATALOG NUMBER: LSR2WM2B20FL408027D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3952.2
2.5°	3934.9
5°	3865.5
7.5°	3689.8
10°	3396.9
12.5°	3045.5
15°	2620.4
17.5°	2156.2
20°	1696.3
22.5°	1286.3
25°	939.3
27.5°	661.6
30°	453.4
32.5°	305.9
35°	201.7
37.5°	121.5
40°	75.9
42.5°	52.1
45°	34.7
47.5°	23.9
50°	17.4
52.5°	15.2
55°	10.8
57.5°	8.7
60°	8.7
62.5°	6.5
65°	4.3
67.5°	4.3
70°	4.3
72.5°	4.3
75°	2.2
77.5°	2.2
80°	2.2
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)