

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL558030D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20WFL558030D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1635.3 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558030D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558030D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			93
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			86
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			80
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			74
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			69
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			64
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			60
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			56
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	767100
5°	762215
10°	708608
15°	622047
20°	536237
25°	458546
30°	363898
35°	253691
40°	160491
45°	97945
50°	57910
55°	31672
60°	6895
65°	6141
70°	5096
75°	6735
80°	4907
85°	9777



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558030D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.9	11.1
10°-20°	432.0	26.4
20°-30°	487.4	29.8
30°-40°	337.2	20.6
40°-50°	143.7	8.8
50°-60°	41.6	2.5
60°-70°	6.1	0.4
70°-80°	3.8	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1101.4	67.4
0°-40°	1438.6	88.0
0°-60°	1623.9	99.3
0°-90°	1635.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1635.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1980	
5°	1960	182
15°	1551	432
25°	1073	487
35°	536	337
45°	179	144
55°	47	42
65°	7	6
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL558030D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1980.4
2.5°	1978.2
5°	1960.3
7.5°	1899.9
10°	1801.6
12.5°	1680.9
15°	1551.2
17.5°	1417.1
20°	1300.9
22.5°	1191.4
25°	1072.9
27.5°	947.7
30°	813.6
32.5°	668.3
35°	536.5
37.5°	415.8
40°	317.4
42.5°	239.2
45°	178.8
47.5°	129.6
50°	96.1
52.5°	69.3
55°	46.9
57.5°	20.1
60°	8.9
62.5°	6.7
65°	6.7
67.5°	4.5
70°	4.5
72.5°	4.5
75°	4.5
77.5°	2.2
80°	2.2
82.5°	2.2
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)