

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224999

Luminaire Tested: **LSRWM2B10FL408027D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL408027D010 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 948.6 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224999

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224999

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	105	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	95	90	87		93	89	86		91	88	85		89	86	84
5	98	91	86	83		97	90	86	83		89	85	82		87	84	81		86	83	81
6	94	87	82	79		93	86	82	79		85	81	78		84	80	78		83	79	77
7	91	83	79	75		90	83	78	75		82	78	75		81	77	74		80	76	74
8	88	80	75	72		87	80	75	72		79	74	71		78	74	71		77	73	71
9	85	77	72	69		84	76	72	69		76	71	69		75	71	68		74	71	68
10	82	74	69	66		81	74	69	66		73	69	66		72	68	66		72	68	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	909953
5°	874430
10°	761195
15°	594417
20°	395305
25°	226345
30°	112533
35°	51731
40°	20731
45°	9477
50°	4399
55°	2431
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224999

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.7	21.6
10°-20°	401.9	42.4
20°-30°	248.7	26.2
30°-40°	74.4	7.8
40°-50°	14.9	1.6
50°-60°	3.6	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	855.4	90.2
0°-40°	929.8	98.0
0°-60°	948.3	100.0
0°-90°	948.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2349	
5°	2249	205
15°	1482	402
25°	530	249
35°	109	74
45°	17	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224999

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2349.2
1°	2336.4
2°	2324.6
3°	2300.9
4°	2279.0
5°	2248.9
6°	2207.9
7°	2155.9
8°	2089.4
9°	2013.7
10°	1935.3
11°	1854.2
12°	1767.6
13°	1677.3
14°	1580.7
15°	1482.3
17.5°	1222.5
20°	959.0
22.5°	725.6
25°	529.6
27.5°	371.9
30°	251.6
32.5°	165.9
35°	109.4
37.5°	68.4
40°	41.0
42.5°	26.4
45°	17.3
47.5°	10.9
50°	7.3
52.5°	5.5
55°	3.6
57.5°	2.7
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224999

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)