

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224796

Luminaire Tested: **LSRWM2B10FL408027D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL408027D010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 940.5 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224796

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224796

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	87	82	78	93	86	81	78	84	80	77		83	80	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	851541
5°	836014
10°	743181
15°	584472
20°	388915
25°	223268
30°	112801
35°	53055
40°	21338
45°	10572
50°	5845
55°	4052
60°	3719
65°	2200
70°	2718
75°	1796
80°	2677
85°	0



TEST NUMBER: P224796

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.9	20.9
10°-20°	394.8	42.0
20°-30°	245.6	26.1
30°-40°	75.5	8.0
40°-50°	16.6	1.8
50°-60°	5.9	0.6
60°-70°	3.0	0.3
70°-80°	1.7	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.3	89.0
0°-40°	912.9	97.1
0°-60°	935.4	99.4
0°-90°	940.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	940.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2198	
5°	2150	197
15°	1458	395
25°	522	246
35°	112	76
45°	19	17
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224796

CATALOG NUMBER: LSRWM2B10FL408027D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2198.4
2.5°	2188.7
5°	2150.1
7.5°	2052.4
10°	1889.5
12.5°	1694.0
15°	1457.5
17.5°	1199.3
20°	943.5
22.5°	715.5
25°	522.4
27.5°	368.0
30°	252.2
32.5°	170.1
35°	112.2
37.5°	67.6
40°	42.2
42.5°	29.0
45°	19.3
47.5°	13.3
50°	9.7
52.5°	8.4
55°	6.0
57.5°	4.8
60°	4.8
62.5°	3.6
65°	2.4
67.5°	2.4
70°	2.4
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)