

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224623

Luminaire Tested: **LSSQWM2B10FL408027D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL408027D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 929.9 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224623

CATALOG NUMBER: LSSQWM2B10FL408027D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224623

CATALOG NUMBER: LSSQWM2B10FL408027D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100	108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93	104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83	96	90	86	82		88	85	82			87	83	81			79
6	94	87	82	78	93	86	82	78		85	81	78			83	80	77			75
7	91	83	78	75	89	82	78	75		81	77	74			80	77	74			72
8	87	80	75	71	86	79	75	71		78	74	71			77	73	71			69
9	84	76	72	68	83	76	71	68		75	71	68			74	71	68			67
10	81	74	69	66	81	73	69	66		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	846467
5°	830182
10°	737478
15°	581986
20°	388173
25°	223396
30°	113159
35°	53055
40°	21743
45°	9805
50°	5062
55°	3242
60°	1859
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224623

CATALOG NUMBER: LSSQWM2B10FL408027D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	21.0
10°-20°	392.2	42.2
20°-30°	245.6	26.4
30°-40°	76.0	8.2
40°-50°	15.7	1.7
50°-60°	4.4	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.2	89.6
0°-40°	909.3	97.8
0°-60°	929.4	99.9
0°-90°	929.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2185	
5°	2135	195
15°	1451	392
25°	523	246
35°	112	76
45°	18	16
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224623

CATALOG NUMBER: LSSQWM2B10FL408027D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2185.3
2.5°	2174.5
5°	2135.1
7.5°	2034.9
10°	1875.0
12.5°	1678.0
15°	1451.3
17.5°	1189.9
20°	941.7
22.5°	716.1
25°	522.7
27.5°	367.6
30°	253.0
32.5°	169.5
35°	112.2
37.5°	70.4
40°	43.0
42.5°	27.5
45°	17.9
47.5°	11.9
50°	8.4
52.5°	6.0
55°	4.8
57.5°	3.6
60°	2.4
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)