

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225284

Luminaire Tested: **LSSQ2B05FL409027D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409027D010 2LBDC*MMS
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 596.0 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225284

CATALOG NUMBER: LSSQ2B05FL409027D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225284

CATALOG NUMBER: LSSQ2B05FL409027D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	539573
5°	529736
10°	470924
15°	370373
20°	246457
25°	141466
30°	71474
35°	33620
40°	13551
45°	6683
50°	3676
55°	2566
60°	2402
65°	1375
70°	1699
75°	1197
80°	1785
85°	0



TEST NUMBER: P225284

CATALOG NUMBER: LSSQ2B05FL409027D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	20.9
10°-20°	250.2	42.0
20°-30°	155.6	26.1
30°-40°	47.9	8.0
40°-50°	10.5	1.8
50°-60°	3.8	0.6
60°-70°	1.9	0.3
70°-80°	1.1	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.6	89.0
0°-40°	578.4	97.1
0°-60°	592.7	99.4
0°-90°	596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1393	
5°	1362	125
15°	924	250
25°	331	156
35°	71	48
45°	12	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225284

CATALOG NUMBER: LSSQ2B05FL409027D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1393.0
2.5°	1386.9
5°	1362.4
7.5°	1300.5
10°	1197.3
12.5°	1073.4
15°	923.6
17.5°	759.9
20°	597.9
22.5°	453.4
25°	331.0
27.5°	233.2
30°	159.8
32.5°	107.8
35°	71.1
37.5°	42.8
40°	26.8
42.5°	18.3
45°	12.2
47.5°	8.4
50°	6.1
52.5°	5.4
55°	3.8
57.5°	3.1
60°	3.1
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)