

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225295

Luminaire Tested: **LSRWM2B10FL409027D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409027D010 2LBDC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 795.1 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225295

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225295

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			85
6	94	87	82	78		93	86	81	78		84	80	77			83	80	77			82
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	719921
5°	706807
10°	628292
15°	494125
20°	328816
25°	188778
30°	95358
35°	44875
40°	18052
45°	8929
50°	4941
55°	3444
60°	3176
65°	1833
70°	2265
75°	1497
80°	2231
85°	0



TEST NUMBER: P225295

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.5	20.9
10°-20°	333.8	42.0
20°-30°	207.7	26.1
30°-40°	63.8	8.0
40°-50°	14.0	1.8
50°-60°	5.0	0.6
60°-70°	2.5	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.9	89.0
0°-40°	771.8	97.1
0°-60°	790.8	99.5
0°-90°	795.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1859	
5°	1818	166
15°	1232	334
25°	442	208
35°	95	64
45°	16	14
55°	5	5
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225295

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1858.6
2.5°	1850.4
5°	1817.8
7.5°	1735.1
10°	1597.4
12.5°	1432.2
15°	1232.2
17.5°	1013.9
20°	797.7
22.5°	604.9
25°	441.7
27.5°	311.1
30°	213.2
32.5°	143.8
35°	94.9
37.5°	57.1
40°	35.7
42.5°	24.5
45°	16.3
47.5°	11.2
50°	8.2
52.5°	7.1
55°	5.1
57.5°	4.1
60°	4.1
62.5°	3.1
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)