

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224571

Luminaire Tested: **LSRWM2B10FL409027D010 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409027D010 2LBDL*GPH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 751.2 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224571

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P224571

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	99	96		98	96	94		95
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89
5	98	91	86	83	96	90	85	82	88	84	81		87	83	81		85
6	94	87	82	78	93	86	81	78	85	81	78		83	80	77		82
7	91	83	78	75	89	82	78	74	81	77	74		80	76	74		79
8	87	80	75	71	86	79	74	71	78	74	71		77	73	71		76
9	84	76	72	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	681458
5°	667691
10°	593286
15°	465452
20°	313070
25°	182153
30°	91243
35°	42558
40°	19872
45°	8381
50°	4037
55°	2566
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224571

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.2	20.9
10°-20°	315.1	41.9
20°-30°	199.2	26.5
30°-40°	62.0	8.2
40°-50°	13.8	1.8
50°-60°	3.5	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.5	89.4
0°-40°	733.5	97.6
0°-60°	750.7	99.9
0°-90°	751.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	751.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1759	
5°	1717	157
15°	1161	315
25°	426	199
35°	90	62
45°	15	14
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224571

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1759.3
2.5°	1751.6
5°	1717.2
7.5°	1635.8
10°	1508.4
12.5°	1347.5
15°	1160.7
17.5°	958.7
20°	759.5
22.5°	580.4
25°	426.2
27.5°	298.8
30°	204.0
32.5°	135.0
35°	90.0
37.5°	60.3
40°	39.3
42.5°	23.9
45°	15.3
47.5°	10.5
50°	6.7
52.5°	4.8
55°	3.8
57.5°	2.9
60°	1.9
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)