

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225438

Luminaire Tested: **LSSQWM2B05FL409027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409027D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 543.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225438

CATALOG NUMBER: LSSQWM2B05FL409027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225438

CATALOG NUMBER: LSSQWM2B05FL409027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91
4	101	94	90	86	99	93	89	86	91	87	85		89	86	84		88
5	97	90	85	81	95	89	84	81	87	83	80		85	82	79		84
6	93	85	80	77	92	85	80	76	83	79	76		82	78	75		81
7	89	81	76	73	88	81	76	73	80	75	72		79	75	72		78
8	86	78	73	69	85	77	73	69	76	72	69		75	72	69		75
9	83	75	70	66	82	74	69	66	73	69	66		72	69	66		72
10	80	72	67	63	79	71	66	63	70	66	63		70	66	63		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	472175
5°	455237
10°	400401
15°	313830
20°	217356
25°	133901
30°	74515
35°	39768
40°	19720
45°	10025
50°	5544
55°	3579
60°	1782
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225438

CATALOG NUMBER: LSSQWM2B05FL409027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.8	19.7
10°-20°	213.8	39.4
20°-30°	146.0	26.9
30°-40°	55.7	10.3
40°-50°	15.5	2.8
50°-60°	4.8	0.9
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.6	85.9
0°-40°	522.2	96.2
0°-60°	542.5	99.9
0°-90°	543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1219	
5°	1171	107
15°	783	214
25°	313	146
35°	84	56
45°	18	15
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225438

CATALOG NUMBER: LSSQWM2B05FL409027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1219.0
2.5°	1206.0
5°	1170.8
7.5°	1105.1
10°	1018.0
12.5°	907.2
15°	782.6
17.5°	655.0
20°	527.3
22.5°	414.2
25°	313.3
27.5°	230.0
30°	166.6
32.5°	118.5
35°	84.1
37.5°	58.8
40°	39.0
42.5°	26.0
45°	18.3
47.5°	13.0
50°	9.2
52.5°	6.9
55°	5.3
57.5°	3.8
60°	2.3
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)