

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B10WFL559027D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10WFL559027D010 2LBDL*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 691.1 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B10WFL559027D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B10WFL559027D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	102	101		101	99	98		97	96	95
2	108	102	98	95		105	101	97	94		98	94	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		86	84	81
4	96	89	83	79		95	87	82	78		85	81	77		83	79	76		81	78	75
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70
6	87	77	71	67		85	77	71	67		75	70	66		74	69	66		72	68	65
7	82	73	66	62		81	72	66	62		71	65	62		69	65	61		68	64	61
8	78	68	62	58		77	68	62	58		67	61	57		66	61	57		65	60	57
9	74	64	58	54		73	64	58	54		63	58	54		62	57	54		61	57	54
10	71	61	55	51		70	60	55	51		60	54	51		59	54	51		58	54	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	324209
5°	317904
10°	295542
15°	261659
20°	226507
25°	190402
30°	149119
35°	106536
40°	71144
45°	44097
50°	26394
55°	15802
60°	7127
65°	917
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B10WFL559027D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	11.0
10°-20°	181.7	26.3
20°-30°	202.7	29.3
30°-40°	142.0	20.5
40°-50°	64.8	9.4
50°-60°	21.7	3.1
60°-70°	2.4	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.3	66.6
0°-40°	602.3	87.1
0°-60°	688.7	99.7
0°-90°	691.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	837	
5°	818	76
15°	652	182
25°	446	203
35°	225	142
45°	80	65
55°	23	22
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B10WFL559027D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	837.0
2.5°	832.9
5°	817.6
7.5°	789.1
10°	751.4
12.5°	703.5
15°	652.5
17.5°	599.5
20°	549.5
22.5°	499.6
25°	445.5
27.5°	390.5
30°	333.4
32.5°	277.3
35°	225.3
37.5°	179.4
40°	140.7
42.5°	107.0
45°	80.5
47.5°	60.2
50°	43.8
52.5°	31.6
55°	23.4
57.5°	16.3
60°	9.2
62.5°	3.1
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)