

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225450

Luminaire Tested: **LSSQ2B10FL409027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL409027D010 2LBDLC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 724.5 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225450

CATALOG NUMBER: LSSQ2B10FL409027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225450

CATALOG NUMBER: LSSQ2B10FL409027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	105	102	99	107	104	101	98		101	98	96			98	96	94			95
3	105	100	95	92	103	98	94	91		96	92	90			93	91	88			91
4	101	94	90	86	99	93	89	86		91	87	85			89	86	84			88
5	97	90	85	81	95	89	84	81		87	83	80			85	82	79			84
6	93	85	80	77	92	85	80	76		83	79	76			82	78	75			81
7	89	81	76	73	88	81	76	73		80	75	72			79	75	72			78
8	86	78	73	69	85	77	73	69		76	72	69			75	72	69			75
9	83	75	70	66	82	74	69	66		73	69	66			72	69	66			72
10	80	72	67	63	79	71	66	63		70	66	63			70	66	63			69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	629980
5°	607423
10°	534248
15°	418735
20°	290027
25°	178691
30°	99428
35°	53055
40°	26294
45°	13421
50°	7352
55°	4795
60°	2402
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225450

CATALOG NUMBER: LSSQ2B10FL409027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.5	19.7
10°-20°	285.2	39.4
20°-30°	194.8	26.9
30°-40°	74.3	10.3
40°-50°	20.6	2.8
50°-60°	6.4	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.5	85.9
0°-40°	696.8	96.2
0°-60°	723.9	99.9
0°-90°	724.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	724.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1626	
5°	1562	142
15°	1044	285
25°	418	195
35°	112	74
45°	24	21
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225450

CATALOG NUMBER: LSSQ2B10FL409027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1626.4
2.5°	1609.1
5°	1562.2
7.5°	1474.5
10°	1358.3
12.5°	1210.4
15°	1044.2
17.5°	873.9
20°	703.6
22.5°	552.7
25°	418.1
27.5°	306.9
30°	222.3
32.5°	158.1
35°	112.2
37.5°	78.5
40°	52.0
42.5°	34.7
45°	24.5
47.5°	17.3
50°	12.2
52.5°	9.2
55°	7.1
57.5°	5.1
60°	3.1
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)