

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B05WFL559727D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05WFL559727D010 2LBDL*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 466.0 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559727D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559727D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	102	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	96	89	83	79	95	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68
8	78	68	62	58	77	68	62	58	67	61	57		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	60	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218618
5°	214360
10°	199257
15°	176444
20°	152722
25°	128388
30°	100546
35°	71828
40°	47986
45°	29745
50°	17837
55°	10670
60°	4803
65°	642
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559727D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	11.0
10°-20°	122.5	26.3
20°-30°	136.7	29.3
30°-40°	95.7	20.5
40°-50°	43.7	9.4
50°-60°	14.6	3.1
60°-70°	1.6	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.4	66.6
0°-40°	406.1	87.1
0°-60°	464.4	99.7
0°-90°	466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	466.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	551	51
15°	440	123
25°	300	137
35°	152	96
45°	54	44
55°	16	15
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559727D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	564.4
2.5°	561.6
5°	551.3
7.5°	532.1
10°	506.6
12.5°	474.3
15°	440.0
17.5°	404.2
20°	370.5
22.5°	336.8
25°	300.4
27.5°	263.3
30°	224.8
32.5°	187.0
35°	151.9
37.5°	121.0
40°	94.9
42.5°	72.2
45°	54.3
47.5°	40.6
50°	29.6
52.5°	21.3
55°	15.8
57.5°	11.0
60°	6.2
62.5°	2.1
65°	0.7
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)