

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224758

Luminaire Tested: **LSSQWM2B05FL409727D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409727D010 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.0 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224758

CATALOG NUMBER: LSSQWM2B05FL409727D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224758

CATALOG NUMBER: LSSQWM2B05FL409727D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	87	82	78	93	86	81	78	84	80	77		83	80	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	452653
5°	444428
10°	395052
15°	310703
20°	206762
25°	118686
30°	59934
35°	28183
40°	11326
45°	5642
50°	3073
55°	2161
60°	2014
65°	1192
70°	1472
75°	898
80°	1338
85°	0



TEST NUMBER: P224758

CATALOG NUMBER: LSSQWM2B05FL409727D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	20.9
10°-20°	209.9	42.0
20°-30°	130.6	26.1
30°-40°	40.1	8.0
40°-50°	8.8	1.8
50°-60°	3.1	0.6
60°-70°	1.6	0.3
70°-80°	0.9	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.1	89.0
0°-40°	485.2	97.1
0°-60°	497.2	99.5
0°-90°	500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1169	
5°	1143	105
15°	775	210
25°	278	131
35°	60	40
45°	10	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224758

CATALOG NUMBER: LSSQWM2B05FL409727D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1168.6
2.5°	1163.5
5°	1143.0
7.5°	1091.0
10°	1004.4
12.5°	900.5
15°	774.8
17.5°	637.5
20°	501.6
22.5°	380.3
25°	277.7
27.5°	195.6
30°	134.0
32.5°	90.4
35°	59.6
37.5°	35.9
40°	22.4
42.5°	15.4
45°	10.3
47.5°	7.1
50°	5.1
52.5°	4.5
55°	3.2
57.5°	2.6
60°	2.6
62.5°	1.9
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)