

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL559727D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14811)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL559727D010 2LBDC*MMS
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 502.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559727D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559727D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93						
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87						
3	102	96	91	87	100	94	90	86	92	88	84	89	86	83	87	84	82	80						
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74						
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69						
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65						
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60						
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56						
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53						
10	71	62	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239651
5°	237378
10°	220339
15°	193407
20°	166448
25°	141637
30°	112175
35°	77880
40°	49452
45°	29800
50°	16993
55°	9319
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559727D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	11.3
10°-20°	134.3	26.7
20°-30°	150.7	30.0
30°-40°	103.8	20.7
40°-50°	43.9	8.7
50°-60°	12.4	2.5
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.6	68.0
0°-40°	445.4	88.7
0°-60°	501.7	99.9
0°-90°	502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	619	
5°	610	57
15°	482	134
25°	331	151
35°	165	104
45°	54	44
55°	14	12
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559727D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	618.7
2.5°	616.7
5°	610.5
7.5°	591.2
10°	560.2
12.5°	522.3
15°	482.3
17.5°	440.3
20°	403.8
22.5°	368.6
25°	331.4
27.5°	292.8
30°	250.8
32.5°	205.3
35°	164.7
37.5°	128.8
40°	97.8
42.5°	73.7
45°	54.4
47.5°	39.3
50°	28.2
52.5°	20.7
55°	13.8
57.5°	6.9
60°	1.4
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)