Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223939

Luminaire Tested: **LSSQWM2B10SP159027D010 2LBD*MW**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-41-14
Report Number:	P223939
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab:	INNOVATION CENTER-P2
Issue Date:	3/3/2020
Manufacturer:	COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line:	io LED
Catalog Number:	LSSQWM2B10SP159027D010 2LBD*MW
Description:	1000 Lumen, 2inch Portfolio LED Cylinder
	SPOT OPTIC
	SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	440.3 lumens
Efficiency:	N/A
Efficacy:	42.7 lumens/watt
Spacing Criteria (0/90/45):	0.24 / 0.24 / 0.23
Luminous Opening:	Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type:	Direct

Input Watts (W):	10.3
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	25 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P223939
CATALOG NUMBER: LSSQWM2B10SP159027D010 2LBD*MW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P223939
CATALOG NUMBER: LSSQWM2B10SP159027D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2115723
5°	1529484
10°	445279
15°	156234
20°	66901
25°	30088
30°	11629
35°	5769
40°	3893
45°	2520
50°	1386
55°	1013
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P223939
CATALOG NUMBER: LSSQWM2B10SP159027D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.4	63.2
10°-20°	113.2	25.7
20°-30°	34.8	7.9
30°-40°	8.6	1.9
40°-50°	3.6	0.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.3	96.8
0°-40°	434.9	98.8
0°-60°	440.0	99.9
0°-90°	440.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5462	
5°	3934	278
15°	390	113
25°	70	35
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P223939
CATALOG NUMBER: LSSQWM2B10SP159027D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5462.1
1°	5378.7
2°	5175.1
3°	4850.5
4°	4426.5
5°	3933.6
6°	3377.9
7°	2774.7
8°	2163.1
9°	1591.3
10°	1132.1
11°	811.4
12°	610.0
13°	496.8
14°	434.8
15°	389.6
17.5°	240.3
20°	162.3
22.5°	108.7
25°	70.4
27.5°	42.9
30°	26.0
32.5°	16.8
35°	12.2
37.5°	10.0
40°	7.7
42.5°	6.1
45°	4.6
47.5°	3.1
50°	2.3
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0

TEST NUMBER: P223939
CATALOG NUMBER: LSSQWM2B10SP159027D010 2LBD*MW

CANDELA DISTRIBUTION (continued):

	0°
90°	*0.0*

Report Generated By E9808895 / USPTCWHP6082093

0°-180°

85°	*0.0*
87.5°	*0.0*

(END OF REPORT)