

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224689

Luminaire Tested: **LSSQWM2B05FL408030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408030D010 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.9 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224689

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224689

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	87	82	78	93	86	81	78	84	80	77		83	80	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	643692
5°	631958
10°	561781
15°	441833
20°	293985
25°	168776
30°	85249
35°	40099
40°	16130
45°	7998
50°	4399
55°	3106
60°	2789
65°	1650
70°	2039
75°	1347
80°	2008
85°	0



TEST NUMBER: P224689

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	20.9
10°-20°	298.4	42.0
20°-30°	185.7	26.1
30°-40°	57.1	8.0
40°-50°	12.5	1.8
50°-60°	4.5	0.6
60°-70°	2.2	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	633.0	89.0
0°-40°	690.0	97.1
0°-60°	707.0	99.5
0°-90°	710.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1662	
5°	1625	149
15°	1102	298
25°	395	186
35°	85	57
45°	15	13
55°	5	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224689

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1661.8
2.5°	1654.5
5°	1625.3
7.5°	1551.4
10°	1428.3
12.5°	1280.5
15°	1101.8
17.5°	906.6
20°	713.2
22.5°	540.8
25°	394.9
27.5°	278.2
30°	190.6
32.5°	128.6
35°	84.8
37.5°	51.1
40°	31.9
42.5°	21.9
45°	14.6
47.5°	10.0
50°	7.3
52.5°	6.4
55°	4.6
57.5°	3.6
60°	3.6
62.5°	2.7
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)