

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL558030D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL558030D010 2LBDL*LI
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 675.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558030D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558030D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	109	106	104		104	103	101			101	99	98			97
2	108	103	99	95		106	101	97	94		98	95	92			95	92	90			92
3	102	96	91	87		100	94	90	86		92	88	85			89	86	83			87
4	97	89	84	79		95	88	83	79		86	81	78			84	80	77			82
5	92	83	78	73		90	83	77	73		81	76	72			79	75	72			77
6	87	78	72	68		86	77	72	68		76	71	67			74	70	67			73
7	83	73	67	63		82	73	67	63		72	66	63			70	66	62			69
8	79	69	63	59		78	69	63	59		68	62	59			66	62	58			66
9	75	65	59	55		74	65	59	55		64	59	55			63	58	55			62
10	72	62	56	52		71	61	56	52		61	55	52			60	55	52			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347566
5°	333185
10°	300891
15°	263624
20°	224940
25°	188692
30°	147196
35°	101476
40°	65178
45°	39441
50°	23140
55°	12966
60°	3719
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558030D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.8	11.7
10°-20°	182.7	27.1
20°-30°	200.8	29.7
30°-40°	135.9	20.1
40°-50°	58.2	8.6
50°-60°	17.8	2.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.4	68.5
0°-40°	598.3	88.6
0°-60°	674.3	99.9
0°-90°	675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	897	
5°	857	79
15°	657	183
25°	442	201
35°	215	136
45°	72	58
55°	19	18
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558030D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	897.3
1°	892.5
2°	885.0
3°	877.5
4°	867.9
5°	856.9
6°	843.2
7°	826.7
8°	806.9
9°	786.3
10°	765.0
11°	742.4
12°	721.9
13°	700.6
14°	679.4
15°	657.4
17.5°	600.5
20°	545.7
22.5°	493.6
25°	441.5
27.5°	388.0
30°	329.1
32.5°	269.4
35°	214.6
37.5°	168.0
40°	128.9
42.5°	97.3
45°	72.0
47.5°	52.8
50°	38.4
52.5°	27.4
55°	19.2
57.5°	12.3
60°	4.8
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558030D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)