

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225378

Luminaire Tested: **LSSQ2B05FL409030D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409030D010 2LBDC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225378

CATALOG NUMBER: LSSQ2B05FL409030D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225378

CATALOG NUMBER: LSSQ2B05FL409030D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100		108	104	101	99		101	99	96			98	96	94			96
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	84	81			85
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75		90	83	78	75		81	77	74			80	77	74			79
8	87	80	75	72		86	79	75	71		78	74	71			77	74	71			76
9	84	77	72	69		83	76	72	68		75	71	68			74	71	68			74
10	82	74	69	66		81	73	69	66		73	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555532
5°	545872
10°	486971
15°	384930
20°	256639
25°	148902
30°	74515
35°	35039
40°	13703
45°	6135
50°	2892
55°	1621
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225378

CATALOG NUMBER: LSSQ2B05FL409030D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	21.0
10°-20°	259.8	42.3
20°-30°	163.4	26.6
30°-40°	49.9	8.1
40°-50°	9.8	1.6
50°-60°	2.2	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.9	89.9
0°-40°	601.9	98.0
0°-60°	613.9	100.0
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1434	
5°	1404	129
15°	960	260
25°	348	163
35°	74	50
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225378

CATALOG NUMBER: LSSQ2B05FL409030D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1434.2
2.5°	1431.0
5°	1403.9
7.5°	1340.2
10°	1238.1
12.5°	1110.6
15°	959.9
17.5°	792.5
20°	622.6
22.5°	477.5
25°	348.4
27.5°	245.5
30°	166.6
32.5°	112.4
35°	74.1
37.5°	45.4
40°	27.1
42.5°	17.5
45°	11.2
47.5°	7.2
50°	4.8
52.5°	3.2
55°	2.4
57.5°	1.6
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)