

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225290

Luminaire Tested: **LSRWM2B10FL408030D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL408030D010 2LBDC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1027.3 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225290

CATALOG NUMBER: LSRWM2B10FL408030D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225290

CATALOG NUMBER: LSRWM2B10FL408030D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	87	82	78		93	86	81	78		84	80	77		83	80	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	930018
5°	913079
10°	811697
15°	638368
20°	424777
25°	243868
30°	123178
35°	57973
40°	23310
45°	11558
50°	6327
55°	4457
60°	4106
65°	2383
70°	2945
75°	1946
80°	2900
85°	0



TEST NUMBER: P225290

CATALOG NUMBER: LSRWM2B10FL408030D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	20.9
10°-20°	431.2	42.0
20°-30°	268.3	26.1
30°-40°	82.5	8.0
40°-50°	18.1	1.8
50°-60°	6.5	0.6
60°-70°	3.2	0.3
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.5	89.0
0°-40°	997.0	97.1
0°-60°	1021.6	99.4
0°-90°	1027.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2401	
5°	2348	215
15°	1592	431
25°	571	268
35°	123	82
45°	21	18
55°	7	6
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P225290

CATALOG NUMBER: LSRWM2B10FL408030D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2401.0
2.5°	2390.5
5°	2348.3
7.5°	2241.6
10°	2063.7
12.5°	1850.2
15°	1591.9
17.5°	1309.9
20°	1030.5
22.5°	781.5
25°	570.6
27.5°	401.9
30°	275.4
32.5°	185.8
35°	122.6
37.5°	73.8
40°	46.1
42.5°	31.6
45°	21.1
47.5°	14.5
50°	10.5
52.5°	9.2
55°	6.6
57.5°	5.3
60°	5.3
62.5°	4.0
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)