

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224624

Luminaire Tested: **LSSQ2B10FL408030D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL408030D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 947.3 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224624

CATALOG NUMBER: LSSQ2B10FL408030D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224624

CATALOG NUMBER: LSSQ2B10FL408030D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83		
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	83	80	79		
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76		
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72		
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69		
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67		
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	862310
5°	845735
10°	751244
15°	592853
20°	395428
25°	227585
30°	115306
35°	54048
40°	22147
45°	9970
50°	5122
55°	3309
60°	1859
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224624

CATALOG NUMBER: LSSQ2B10FL408030D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.1	21.0
10°-20°	399.5	42.2
20°-30°	250.2	26.4
30°-40°	77.4	8.2
40°-50°	16.0	1.7
50°-60°	4.4	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.8	89.6
0°-40°	926.3	97.8
0°-60°	946.7	99.9
0°-90°	947.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2226	
5°	2175	199
15°	1478	400
25°	532	250
35°	114	77
45°	18	16
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224624

CATALOG NUMBER: LSSQ2B10FL408030D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2226.2
2.5°	2215.2
5°	2175.1
7.5°	2073.0
10°	1910.0
12.5°	1709.4
15°	1478.4
17.5°	1212.2
20°	959.3
22.5°	729.5
25°	532.5
27.5°	374.5
30°	257.8
32.5°	172.6
35°	114.3
37.5°	71.7
40°	43.8
42.5°	28.0
45°	18.2
47.5°	12.2
50°	8.5
52.5°	6.1
55°	4.9
57.5°	3.6
60°	2.4
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)