

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225434

Luminaire Tested: **LSSQWM2B05FL408035D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408035D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225434

CATALOG NUMBER: LSSQWM2B05FL408035D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225434

CATALOG NUMBER: LSSQWM2B05FL408035D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91
4	101	94	90	86	99	93	89	86	91	87	85		89	86	84		88
5	97	90	85	81	95	89	84	81	87	83	80		85	82	79		84
6	93	85	80	77	92	85	80	76	83	79	76		82	78	75		81
7	89	81	76	73	88	81	76	73	80	75	72		79	75	72		78
8	86	78	73	69	85	77	73	69	76	72	69		75	72	69		75
9	83	75	70	66	82	74	69	66	73	69	66		72	69	66		72
10	80	72	67	63	79	71	66	63	70	66	63		70	66	63		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	617391
5°	595253
10°	523550
15°	410354
20°	284215
25°	175101
30°	97415
35°	51968
40°	25788
45°	13147
50°	7231
55°	4727
60°	2324
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225434

CATALOG NUMBER: LSSQWM2B05FL408035D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.6	19.7
10°-20°	279.5	39.4
20°-30°	190.9	26.9
30°-40°	72.8	10.3
40°-50°	20.2	2.8
50°-60°	6.3	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.1	85.9
0°-40°	682.9	96.2
0°-60°	709.4	99.9
0°-90°	710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1594	
5°	1531	140
15°	1023	280
25°	410	191
35°	110	73
45°	24	20
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225434

CATALOG NUMBER: LSSQWM2B05FL408035D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1593.9
2.5°	1576.9
5°	1530.9
7.5°	1445.0
10°	1331.1
12.5°	1186.2
15°	1023.3
17.5°	856.4
20°	689.5
22.5°	541.6
25°	409.7
27.5°	300.8
30°	217.8
32.5°	154.9
35°	109.9
37.5°	76.9
40°	51.0
42.5°	34.0
45°	24.0
47.5°	17.0
50°	12.0
52.5°	9.0
55°	7.0
57.5°	5.0
60°	3.0
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)