

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225000

Luminaire Tested: **LSSQWM2B10FL408030D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL408030D010 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 967.3 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225000

CATALOG NUMBER: LSSQWM2B10FL408030D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P225000

CATALOG NUMBER: LSSQWM2B10FL408030D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	105	103			102	101	100			96
2	110	106	103	100		108	104	101	99		101	99	97			98	96	95			91
3	106	101	96	93		104	99	95	92		97	94	91			94	92	90			87
4	102	96	91	88		100	95	90	87		93	89	86			91	88	85			83
5	98	91	86	83		97	90	86	83		89	85	82			87	84	81			79
6	94	87	82	79		93	86	82	79		85	81	78			84	80	78			76
7	91	83	79	75		90	83	78	75		82	78	75			81	77	74			73
8	88	80	75	72		87	80	75	72		79	74	71			78	74	71			70
9	85	77	72	69		84	76	72	69		76	71	69			75	71	68			67
10	82	74	69	66		81	74	69	66		73	69	66			72	68	66			65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	927887
5°	891694
10°	776220
15°	606127
20°	403095
25°	230833
30°	114769
35°	52724
40°	21136
45°	9696
50°	4459
55°	2499
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225000

CATALOG NUMBER: LSSQWM2B10FL408030D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.7	21.6
10°-20°	409.9	42.4
20°-30°	253.7	26.2
30°-40°	75.9	7.8
40°-50°	15.2	1.6
50°-60°	3.7	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	872.3	90.2
0°-40°	948.2	98.0
0°-60°	967.1	100.0
0°-90°	967.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	967.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2396	
5°	2293	209
15°	1512	410
25°	540	254
35°	112	76
45°	18	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225000

CATALOG NUMBER: LSSQWM2B10FL408030D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2395.5
1°	2382.5
2°	2370.4
3°	2346.2
4°	2323.9
5°	2293.3
6°	2251.4
7°	2198.4
8°	2130.6
9°	2053.4
10°	1973.5
11°	1890.8
12°	1802.4
13°	1710.4
14°	1611.9
15°	1511.5
17.5°	1246.6
20°	977.9
22.5°	739.9
25°	540.1
27.5°	379.3
30°	256.6
32.5°	169.2
35°	111.5
37.5°	69.7
40°	41.8
42.5°	27.0
45°	17.7
47.5°	11.2
50°	7.4
52.5°	5.6
55°	3.7
57.5°	2.8
60°	1.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P225000

CATALOG NUMBER: LSSQWM2B10FL408030D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)