

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL558035D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL558035D010 2LBD*WMH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 728.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	87	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	78	76
5	92	83	77	73		90	82	77	72		80	75	72		79	74	71		77	73	70
6	87	78	72	67		85	77	71	67		75	70	67		74	70	66		73	69	66
7	82	73	67	63		81	72	67	62		71	66	62		70	65	62		69	65	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	58
9	75	65	59	55		73	64	59	55		63	58	54		62	58	54		62	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	346713
5°	342594
10°	316663
15°	277539
20°	239491
25°	203865
30°	161464
35°	112068
40°	72813
45°	43823
50°	25309
55°	14182
60°	6198
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.7	11.2
10°-20°	192.8	26.5
20°-30°	217.0	29.8
30°-40°	149.9	20.6
40°-50°	64.9	8.9
50°-60°	20.1	2.8
60°-70°	1.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.5	67.5
0°-40°	641.4	88.1
0°-60°	726.5	99.8
0°-90°	728.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	895	
5°	881	82
15°	692	193
25°	477	217
35°	237	150
45°	80	65
55°	21	20
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL558035D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	895.1
2.5°	893.1
5°	881.1
7.5°	853.1
10°	805.1
12.5°	750.1
15°	692.1
17.5°	632.1
20°	581.0
22.5°	530.0
25°	477.0
27.5°	423.0
30°	361.0
32.5°	296.0
35°	237.0
37.5°	186.0
40°	144.0
42.5°	109.0
45°	80.0
47.5°	59.0
50°	42.0
52.5°	30.0
55°	21.0
57.5°	15.0
60°	8.0
62.5°	2.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)