

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225286

Luminaire Tested: **LSSQ2B05FL409035D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409035D010 2LBDC*MMS
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 645.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225286

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225286

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78	93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	583924
5°	573284
10°	509627
15°	400810
20°	266697
25°	153133
30°	77333
35°	36363
40°	14664
45°	7231
50°	3977
55°	2769
60°	2556
65°	1558
70°	1925
75°	1197
80°	1785
85°	0



TEST NUMBER: P225286

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.0	20.9
10°-20°	270.7	42.0
20°-30°	168.4	26.1
30°-40°	51.8	8.0
40°-50°	11.4	1.8
50°-60°	4.0	0.6
60°-70°	2.1	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	89.0
0°-40°	626.0	97.1
0°-60°	641.4	99.4
0°-90°	645.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1508	
5°	1474	135
15°	1000	271
25°	358	168
35°	77	52
45°	13	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225286

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1507.5
2.5°	1500.9
5°	1474.4
7.5°	1407.4
10°	1295.7
12.5°	1161.7
15°	999.5
17.5°	822.4
20°	647.0
22.5°	490.6
25°	358.3
27.5°	252.4
30°	172.9
32.5°	116.7
35°	76.9
37.5°	46.3
40°	29.0
42.5°	19.9
45°	13.2
47.5°	9.1
50°	6.6
52.5°	5.8
55°	4.1
57.5°	3.3
60°	3.3
62.5°	2.5
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)