

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224179

Luminaire Tested: **LSSQWM2B10SP158030D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP158030D010 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 544.4 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224179

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224179

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	102		102	101	100		100	99	98
3	110	106	103	101		108	105	102	100		102	100	98		100	99	97		98	97	96
4	108	103	100	97		106	102	99	97		100	98	96		98	96	95		97	95	94
5	105	101	97	95		104	100	97	94		98	96	94		97	95	93		96	94	92
6	103	98	95	93		102	98	95	92		96	94	92		95	93	91		94	92	91
7	101	96	93	91		100	96	93	90		95	92	90		94	91	90		93	91	89
8	100	94	91	89		99	94	91	89		93	90	89		92	90	88		92	90	88
9	98	93	90	88		97	92	89	87		92	89	87		91	89	87		90	88	87
10	96	91	88	86		96	91	88	86		90	88	86		90	87	86		89	87	86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2615941
5°	1891092
10°	550532
15°	193167
20°	82688
25°	37226
30°	14402
35°	7140
40°	4804
45°	3122
50°	1687
55°	1283
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224179

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.2	63.2
10°-20°	140.0	25.7
20°-30°	43.0	7.9
30°-40°	10.6	1.9
40°-50°	4.4	0.8
50°-60°	1.9	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.2	96.8
0°-40°	537.7	98.8
0°-60°	544.1	99.9
0°-90°	544.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6754	
5°	4864	344
15°	482	140
25°	87	43
35°	15	11
45°	6	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224179

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6753.5
1°	6650.4
2°	6398.6
3°	5997.4
4°	5473.1
5°	4863.6
6°	4176.5
7°	3430.7
8°	2674.5
9°	1967.6
10°	1399.7
11°	1003.2
12°	754.3
13°	614.2
14°	537.6
15°	481.7
17.5°	297.2
20°	200.6
22.5°	134.4
25°	87.1
27.5°	53.0
30°	32.2
32.5°	20.8
35°	15.1
37.5°	12.3
40°	9.5
42.5°	7.6
45°	5.7
47.5°	3.8
50°	2.8
52.5°	2.8
55°	1.9
57.5°	1.9
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224179

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)