

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224961

Luminaire Tested: **LSSQ2B05FL409035D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409035D010 2LBDL*LI
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224961

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224961

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	105	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	96	93	104	99	95	92	97	94	91		94	92	90		92
4	102	96	91	88	100	95	90	87	93	89	86		91	88	85		89
5	98	91	86	83	97	90	86	83	89	85	82		87	84	81		86
6	94	87	82	79	93	86	82	79	85	81	78		84	80	78		83
7	91	83	79	75	90	83	78	75	82	78	75		81	77	74		80
8	88	80	75	72	87	80	75	72	79	74	71		78	74	71		77
9	85	77	72	69	84	76	72	69	76	71	69		75	71	68		74
10	82	74	69	66	81	74	69	66	73	69	66		72	68	66		72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	582258
5°	559559
10°	487089
15°	380358
20°	252970
25°	144842
30°	72010
35°	33100
40°	13248
45°	6080
50°	2832
55°	1553
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224961

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	21.6
10°-20°	257.2	42.4
20°-30°	159.2	26.2
30°-40°	47.6	7.8
40°-50°	9.5	1.6
50°-60°	2.3	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.4	90.2
0°-40°	595.0	98.0
0°-60°	606.8	100.0
0°-90°	607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1503	
5°	1439	131
15°	948	257
25°	339	159
35°	70	48
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224961

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1503.2
1°	1495.1
2°	1487.5
3°	1472.3
4°	1458.3
5°	1439.1
6°	1412.8
7°	1379.6
8°	1337.0
9°	1288.6
10°	1238.4
11°	1186.5
12°	1131.1
13°	1073.3
14°	1011.5
15°	948.5
17.5°	782.2
20°	613.7
22.5°	464.3
25°	338.9
27.5°	238.0
30°	161.0
32.5°	106.2
35°	70.0
37.5°	43.7
40°	26.2
42.5°	16.9
45°	11.1
47.5°	7.0
50°	4.7
52.5°	3.5
55°	2.3
57.5°	1.7
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224961

CATALOG NUMBER: LSSQ2B05FL409035D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)