

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225296

Luminaire Tested: **LSSQ2B10FL409030D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL409030D010 2LBDC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.5 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225296

CATALOG NUMBER: LSSQ2B10FL409030D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225296

CATALOG NUMBER: LSSQ2B10FL409030D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	750057
5°	736397
10°	654605
15°	514817
20°	342584
25°	196684
30°	99338
35°	46719
40°	18810
45°	9312
50°	5122
55°	3579
60°	3331
65°	1925
70°	2378
75°	1646
80°	2454
85°	0



TEST NUMBER: P225296

CATALOG NUMBER: LSSQ2B10FL409030D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	20.9
10°-20°	347.8	42.0
20°-30°	216.3	26.1
30°-40°	66.5	8.0
40°-50°	14.6	1.8
50°-60°	5.2	0.6
60°-70°	2.6	0.3
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.6	89.0
0°-40°	804.1	97.0
0°-60°	823.9	99.4
0°-90°	828.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1936	
5°	1894	173
15°	1284	348
25°	460	216
35°	99	67
45°	17	15
55°	5	5
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P225296

CATALOG NUMBER: LSSQ2B10FL409030D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1936.4
2.5°	1927.9
5°	1893.9
7.5°	1807.8
10°	1664.3
12.5°	1492.1
15°	1283.8
17.5°	1056.4
20°	831.1
22.5°	630.2
25°	460.2
27.5°	324.1
30°	222.1
32.5°	149.9
35°	98.8
37.5°	59.5
40°	37.2
42.5°	25.5
45°	17.0
47.5°	11.7
50°	8.5
52.5°	7.4
55°	5.3
57.5°	4.3
60°	4.3
62.5°	3.2
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)