

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223201

Luminaire Tested: **LSSQ2B05NFL258040D010 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223201  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B05NFL258040D010 2LBDL\*GPH  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 755.0 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223201

CATALOG NUMBER: LSSQ2B05NFL258040D010 2LBDL\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P223201

CATALOG NUMBER: LSSQ2B05NFL258040D010 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 |
| 1   | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  | 97  | 97  |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 95  | 95  | 95  |
| 3   | 109 | 105 | 101 | 99  | 107 | 103 | 100 | 98  | 101 | 98  | 96  | 99  | 97  | 95  | 96  | 95  | 93  | 92  | 92  | 92  |
| 4   | 106 | 101 | 97  | 95  | 104 | 100 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 95  | 93  | 91  | 90  | 90  | 90  |
| 5   | 103 | 98  | 94  | 91  | 102 | 97  | 94  | 91  | 95  | 92  | 90  | 94  | 91  | 89  | 93  | 90  | 89  | 88  | 88  | 88  |
| 6   | 101 | 95  | 91  | 89  | 99  | 94  | 91  | 88  | 93  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 87  | 86  | 86  | 86  |
| 7   | 98  | 92  | 89  | 86  | 97  | 92  | 88  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 87  | 85  | 84  | 84  | 84  |
| 8   | 96  | 90  | 86  | 84  | 95  | 90  | 86  | 84  | 89  | 86  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  | 82  | 82  |
| 9   | 94  | 88  | 84  | 82  | 93  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 80  |
| 10  | 92  | 86  | 82  | 80  | 91  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 84  | 81  | 79  | 79  | 79  | 79  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1734961 |
| 5°  | 1601923 |
| 10° | 1084309 |
| 15° | 368889  |
| 20° | 135492  |
| 25° | 71844   |
| 30° | 36900   |
| 35° | 17212   |
| 40° | 5663    |
| 45° | 2849    |
| 50° | 1326    |
| 55° | 473     |
| 60° | 542     |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P223201

CATALOG NUMBER: LSSQ2B05NFL258040D010 2LBDL\*GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 350.5  | 46.4      |
| 10°-20°   | 294.7  | 39.0      |
| 20°-30°   | 80.9   | 10.7      |
| 30°-40°   | 23.6   | 3.1       |
| 40°-50°   | 4.4    | 0.6       |
| 50°-60°   | 1.0    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 726.0  | 96.2      |
| 0°-40°    | 749.6  | 99.3      |
| 0°-60°    | 754.9  | 100.0     |
| 0°-90°    | 755.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 755.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4479 |      |
| 5°  | 4120 | 350  |
| 15° | 920  | 295  |
| 25° | 168  | 81   |
| 35° | 36   | 24   |
| 45° | 5    | 4    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P223201

CATALOG NUMBER: LSSQ2B05NFL258040D010 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4479.1 |
| 1°    | 4453.1 |
| 2°    | 4407.0 |
| 3°    | 4340.8 |
| 4°    | 4250.1 |
| 5°    | 4119.9 |
| 6°    | 3942.2 |
| 7°    | 3719.8 |
| 8°    | 3448.4 |
| 9°    | 3127.9 |
| 10°   | 2756.8 |
| 11°   | 2350.0 |
| 12°   | 1926.9 |
| 13°   | 1523.0 |
| 14°   | 1178.7 |
| 15°   | 919.9  |
| 17.5° | 519.1  |
| 20°   | 328.7  |
| 22.5° | 234.3  |
| 25°   | 168.1  |
| 27.5° | 119.0  |
| 30°   | 82.5   |
| 32.5° | 58.0   |
| 35°   | 36.4   |
| 37.5° | 14.9   |
| 40°   | 11.2   |
| 42.5° | 8.2    |
| 45°   | 5.2    |
| 47.5° | 3.0    |
| 50°   | 2.2    |
| 52.5° | 1.5    |
| 55°   | 0.7    |
| 57.5° | 0.7    |
| 60°   | 0.7    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P223201

CATALOG NUMBER: LSSQ2B05NFL258040D010 2LBDL\*GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







|       |     |
|-------|-----|
| 85°   | 0.0 |
| 87.5° | 0.0 |



(END OF REPORT)