

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B05WFL558040D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05WFL558040D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.9 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558040D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558040D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			93
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			86
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			80
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			74
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			69
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			64
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			60
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			56
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357443
5°	355153
10°	330193
15°	289850
20°	249879
25°	213652
30°	169560
35°	118216
40°	74785
45°	45631
50°	26997
55°	14789
60°	3254
65°	2841
70°	2378
75°	3143
80°	2231
85°	4444



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558040D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.8	11.1
10°-20°	201.3	26.4
20°-30°	227.1	29.8
30°-40°	157.1	20.6
40°-50°	67.0	8.8
50°-60°	19.4	2.5
60°-70°	2.8	0.4
70°-80°	1.8	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.2	67.4
0°-40°	670.3	88.0
0°-60°	756.7	99.3
0°-90°	761.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	923	
5°	913	85
15°	723	201
25°	500	227
35°	250	157
45°	83	67
55°	22	19
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL558040D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	922.8
2.5°	921.8
5°	913.4
7.5°	885.3
10°	839.5
12.5°	783.2
15°	722.8
17.5°	660.3
20°	606.2
22.5°	555.1
25°	499.9
27.5°	441.6
30°	379.1
32.5°	311.4
35°	250.0
37.5°	193.7
40°	147.9
42.5°	111.4
45°	83.3
47.5°	60.4
50°	44.8
52.5°	32.3
55°	21.9
57.5°	9.4
60°	4.2
62.5°	3.1
65°	3.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)