

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224913

Luminaire Tested: **LSSQWM2B10FL409030D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D010 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 824.5 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224913

CATALOG NUMBER: LSSQWM2B10FL409030D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224913

CATALOG NUMBER: LSSQWM2B10FL409030D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	94		96	94	93
3	106	100	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	94	90	87		92	89	86		91	88	85		89	86	84
5	98	91	86	83		96	90	86	82		89	85	82		87	84	81		86	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		82	77	74		80	77	74		79	76	74
8	88	80	75	72		87	79	75	72		78	74	71		77	74	71		77	73	71
9	85	77	72	69		84	76	72	69		75	71	68		75	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	69	66		72	68	66		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	764737
5°	748723
10°	659443
15°	517383
20°	343573
25°	197240
30°	98891
35°	45678
40°	18557
45°	8326
50°	4339
55°	2701
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224913

CATALOG NUMBER: LSSQWM2B10FL409030D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.9	21.3
10°-20°	349.2	42.4
20°-30°	217.0	26.3
30°-40°	65.4	7.9
40°-50°	13.4	1.6
50°-60°	3.5	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.0	90.0
0°-40°	807.5	97.9
0°-60°	824.3	100.0
0°-90°	824.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1974	
5°	1926	176
15°	1290	349
25°	462	217
35°	97	65
45°	15	13
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224913

CATALOG NUMBER: LSSQWM2B10FL409030D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1974.3
1°	1968.0
2°	1959.2
3°	1952.8
4°	1943.2
5°	1925.6
6°	1897.7
7°	1859.4
8°	1804.3
9°	1742.0
10°	1676.6
11°	1607.1
12°	1534.5
13°	1458.6
14°	1375.6
15°	1290.2
17.5°	1061.0
20°	833.5
22.5°	632.3
25°	461.5
27.5°	325.7
30°	221.1
32.5°	145.3
35°	96.6
37.5°	59.9
40°	36.7
42.5°	24.0
45°	15.2
47.5°	9.6
50°	7.2
52.5°	4.8
55°	4.0
57.5°	2.4
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224913

CATALOG NUMBER: LSSQWM2B10FL409030D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)