

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223825

Luminaire Tested: **LSSQWM2B10SP159030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP159030D010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 447.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223825

CATALOG NUMBER: LSSQWM2B10SP159030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223825

CATALOG NUMBER: LSSQWM2B10SP159030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111	113	112	110	109		108	107	106			104	103	103			98
2	113	110	107	105	111	108	106	104		105	103	102			102	101	100			96
3	110	106	103	101	108	105	102	100		102	100	98			100	98	97			94
4	108	103	100	97	106	102	99	97		100	98	96			98	96	95			93
5	105	101	97	95	104	100	97	94		98	96	94			97	95	93			91
6	103	98	95	93	102	98	95	92		96	94	92			95	93	91			90
7	101	96	93	91	100	96	93	90		95	92	90			94	91	90			88
8	100	94	91	89	99	94	91	89		93	90	89			92	90	88			87
9	98	93	90	88	97	92	89	87		92	89	87			91	89	87			86
10	96	91	88	86	96	91	88	86		90	88	86			90	87	86			85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2147911
5°	1552736
10°	452044
15°	158599
20°	67890
25°	30558
30°	11808
35°	5863
40°	3944
45°	2575
50°	1386
55°	1081
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223825

CATALOG NUMBER: LSSQWM2B10SP159030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.6	63.2
10°-20°	115.0	25.7
20°-30°	35.3	7.9
30°-40°	8.7	1.9
40°-50°	3.6	0.8
50°-60°	1.6	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.8	96.8
0°-40°	441.5	98.8
0°-60°	446.7	99.9
0°-90°	447.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	447.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5545	
5°	3993	283
15°	396	115
25°	72	35
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223825

CATALOG NUMBER: LSSQWM2B10SP159030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5545.2
1°	5460.5
2°	5253.8
3°	4924.4
4°	4493.9
5°	3993.4
6°	3429.3
7°	2816.9
8°	2196.0
9°	1615.5
10°	1149.3
11°	823.7
12°	619.3
13°	504.3
14°	441.4
15°	395.5
17.5°	244.0
20°	164.7
22.5°	110.3
25°	71.5
27.5°	43.5
30°	26.4
32.5°	17.1
35°	12.4
37.5°	10.1
40°	7.8
42.5°	6.2
45°	4.7
47.5°	3.1
50°	2.3
52.5°	2.3
55°	1.6
57.5°	1.6
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223825

CATALOG NUMBER: LSSQWM2B10SP159030D010 2LBDLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)