

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224024

Luminaire Tested: **LSSQWM2B05SP158040D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05SP158040D010 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 437.0 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224024

CATALOG NUMBER: LSSQWM2B05SP158040D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224024

CATALOG NUMBER: LSSQWM2B05SP158040D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	102		102	101	100		100	99	98
3	110	106	103	101		108	105	102	100		102	100	98		100	98	97		98	97	96
4	108	103	100	97		106	102	99	97		100	98	96		98	96	95		97	95	94
5	105	101	97	95		104	100	97	94		98	96	94		97	95	93		95	94	92
6	103	98	95	93		102	98	95	92		96	94	92		95	93	91		94	92	91
7	101	96	93	91		100	96	93	90		95	92	90		94	91	90		93	91	89
8	100	94	91	89		99	94	91	89		93	90	89		92	90	88		92	89	88
9	98	93	90	88		97	92	89	87		92	89	87		91	89	87		90	88	87
10	96	91	88	86		96	91	88	86		90	88	86		90	87	86		89	87	86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2099880
5°	1518014
10°	441936
15°	155071
20°	66406
25°	29874
30°	11540
35°	5769
40°	3843
45°	2520
50°	1386
55°	1013
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224024

CATALOG NUMBER: LSSQWM2B05SP158040D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.3	63.2
10°-20°	112.4	25.7
20°-30°	34.5	7.9
30°-40°	8.5	1.9
40°-50°	3.6	0.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.1	96.8
0°-40°	431.7	98.8
0°-60°	436.7	99.9
0°-90°	437.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	437.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5421	
5°	3904	276
15°	387	112
25°	70	34
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224024

CATALOG NUMBER: LSSQWM2B05SP158040D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5421.2
1°	5338.4
2°	5136.3
3°	4814.2
4°	4393.3
5°	3904.1
6°	3352.5
7°	2753.9
8°	2146.9
9°	1579.4
10°	1123.6
11°	805.3
12°	605.5
13°	493.0
14°	431.5
15°	386.7
17.5°	238.5
20°	161.1
22.5°	107.9
25°	69.9
27.5°	42.5
30°	25.8
32.5°	16.7
35°	12.2
37.5°	9.9
40°	7.6
42.5°	6.1
45°	4.6
47.5°	3.0
50°	2.3
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224024

CATALOG NUMBER: LSSQWM2B05SP158040D010 2LBDLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)