

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B10FL409730D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10FL409730D010 2LBD*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.8 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10FL409730D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B10FL409730D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108	112	110	108	106		106	105	103		102	101	100		99	98	97
2	110	106	103	100	108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	96	93	104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88	100	95	90	87		93	89	86		91	88	85		89	86	84
5	98	91	86	83	97	90	86	83		89	85	82		87	84	81		86	83	81
6	94	87	82	79	93	86	82	79		85	81	78		84	80	78		83	79	77
7	91	83	79	75	90	83	78	75		82	78	75		81	77	74		80	76	74
8	88	80	75	72	87	80	75	72		79	74	71		78	74	71		77	73	71
9	85	77	72	69	84	76	72	69		76	71	69		75	71	68		74	71	68
10	82	74	69	66	81	74	69	66		73	69	66		72	68	66		72	68	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	730767
5°	702258
10°	611300
15°	477362
20°	317480
25°	181769
30°	90393
35°	41565
40°	16636
45°	7614
50°	3555
55°	1958
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10FL409730D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	21.6
10°-20°	322.8	42.4
20°-30°	199.8	26.2
30°-40°	59.8	7.8
40°-50°	12.0	1.6
50°-60°	2.9	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.9	90.2
0°-40°	746.7	98.0
0°-60°	761.6	100.0
0°-90°	761.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1887	
5°	1806	164
15°	1190	323
25°	425	200
35°	88	60
45°	14	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10FL409730D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1886.6
1°	1876.3
2°	1866.8
3°	1847.8
4°	1830.2
5°	1806.1
6°	1773.1
7°	1731.4
8°	1677.9
9°	1617.2
10°	1554.2
11°	1489.1
12°	1419.5
13°	1347.0
14°	1269.4
15°	1190.4
17.5°	981.7
20°	770.2
22.5°	582.7
25°	425.3
27.5°	298.7
30°	202.1
32.5°	133.2
35°	87.9
37.5°	54.9
40°	32.9
42.5°	21.2
45°	13.9
47.5°	8.8
50°	5.9
52.5°	4.4
55°	2.9
57.5°	2.2
60°	1.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10FL409730D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)