

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225427

Luminaire Tested: **LSSQWM2B10FL409730D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409730D010 2LBDLC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 693.8 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225427

CATALOG NUMBER: LSSQWM2B10FL409730D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225427

CATALOG NUMBER: LSSQWM2B10FL409730D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	105	102	99	107	104	101	98		101	98	96			98	96	94			90
3	105	100	95	92	103	98	94	91		96	92	90			93	91	88			86
4	101	94	90	86	99	93	89	86		91	87	85			89	86	84			81
5	97	90	85	81	95	89	84	81		87	83	80			85	82	79			77
6	93	85	80	77	92	85	80	76		83	79	76			82	78	75			74
7	89	81	76	73	88	81	76	73		80	75	72			79	75	72			70
8	86	78	73	69	85	77	73	69		76	72	69			75	72	69			67
9	83	75	70	66	82	74	69	66		73	69	66			72	69	66			64
10	80	72	67	63	79	71	66	63		70	66	63			70	66	63			62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603291
5°	581683
10°	511593
15°	400970
20°	277744
25°	171127
30°	95223
35°	50785
40°	25181
45°	12818
50°	7050
55°	4592
60°	2247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225427

CATALOG NUMBER: LSSQWM2B10FL409730D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	19.7
10°-20°	273.1	39.4
20°-30°	186.6	26.9
30°-40°	71.1	10.3
40°-50°	19.7	2.8
50°-60°	6.2	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.2	85.9
0°-40°	667.3	96.2
0°-60°	693.2	99.9
0°-90°	693.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	693.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1558	
5°	1496	136
15°	1000	273
25°	400	187
35°	107	71
45°	23	20
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225427

CATALOG NUMBER: LSSQWM2B10FL409730D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1557.5
2.5°	1540.9
5°	1496.0
7.5°	1412.0
10°	1300.7
12.5°	1159.1
15°	999.9
17.5°	836.9
20°	673.8
22.5°	529.3
25°	400.4
27.5°	293.9
30°	212.9
32.5°	151.4
35°	107.4
37.5°	75.2
40°	49.8
42.5°	33.2
45°	23.4
47.5°	16.6
50°	11.7
52.5°	8.8
55°	6.8
57.5°	4.9
60°	2.9
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)