

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224943

Luminaire Tested: **LSR2B10FL408040D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224943
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10FL408040D010 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1075.4 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224943

CATALOG NUMBER: LSR2B10FL408040D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224943

CATALOG NUMBER: LSR2B10FL408040D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	94		96	94	93
3	106	100	96	93		104	99	95	92		97	94	91		94	92	90		92	90	88
4	102	96	91	88		100	94	90	87		92	89	86		91	88	85		89	86	84
5	98	91	86	83		96	90	86	82		89	85	82		87	84	81		86	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		82	77	74		80	77	74		79	76	74
8	88	80	75	72		87	79	75	72		78	74	71		77	74	71		77	73	71
9	85	77	72	69		84	76	72	69		75	71	68		75	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	69	66		72	68	66		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	997493
5°	976574
10°	860076
15°	674820
20°	448108
25°	257245
30°	128992
35°	59581
40°	24220
45°	10846
50°	5664
55°	3512
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224943

CATALOG NUMBER: LSR2B10FL408040D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.4	21.3
10°-20°	455.5	42.4
20°-30°	283.0	26.3
30°-40°	85.4	7.9
40°-50°	17.4	1.6
50°-60°	4.5	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.9	90.0
0°-40°	1053.2	97.9
0°-60°	1075.1	100.0
0°-90°	1075.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2575	
5°	2512	229
15°	1683	455
25°	602	283
35°	126	85
45°	20	17
55°	5	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224943

CATALOG NUMBER: LSR2B10FL408040D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2575.2
1°	2566.8
2°	2555.4
3°	2547.0
4°	2534.5
5°	2511.6
6°	2475.2
7°	2425.2
8°	2353.4
9°	2272.1
10°	2186.7
11°	2096.2
12°	2001.4
13°	1902.5
14°	1794.2
15°	1682.8
17.5°	1383.9
20°	1087.1
22.5°	824.7
25°	601.9
27.5°	424.9
30°	288.4
32.5°	189.5
35°	126.0
37.5°	78.1
40°	47.9
42.5°	31.2
45°	19.8
47.5°	12.5
50°	9.4
52.5°	6.2
55°	5.2
57.5°	3.1
60°	2.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224943

CATALOG NUMBER: LSR2B10FL408040D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)