

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B05WFL559040D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05WFL559040D010 2LBDL*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 572.9 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559040D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559040D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	111	108	106		111	108	106	104		104	102	101			101	99	98			93
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			86
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			80
4	96	89	83	79		95	87	82	78		85	81	77			83	79	76			74
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			68
6	87	77	71	67		85	77	71	67		75	70	66			74	69	66			64
7	82	73	66	62		81	72	66	62		71	65	62			69	65	61			59
8	78	68	62	58		77	68	62	58		67	61	57			66	61	57			56
9	74	64	58	54		73	64	58	54		63	58	54			62	57	54			52
10	71	61	55	51		70	60	55	51		60	54	51			59	54	51			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	268818
5°	263585
10°	245039
15°	216946
20°	187801
25°	157878
30°	123625
35°	88331
40°	58958
45°	36592
50°	21875
55°	13101
60°	5888
65°	733
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559040D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	11.0
10°-20°	150.7	26.3
20°-30°	168.0	29.3
30°-40°	117.7	20.5
40°-50°	53.7	9.4
50°-60°	17.9	3.1
60°-70°	1.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.6	66.6
0°-40°	499.3	87.2
0°-60°	571.0	99.7
0°-90°	572.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	678	63
15°	541	151
25°	369	168
35°	187	118
45°	67	54
55°	19	18
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B05WFL559040D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	694.0
2.5°	690.6
5°	677.9
7.5°	654.2
10°	623.0
12.5°	583.2
15°	541.0
17.5°	497.0
20°	455.6
22.5°	414.2
25°	369.4
27.5°	323.7
30°	276.4
32.5°	229.9
35°	186.8
37.5°	148.8
40°	116.6
42.5°	88.8
45°	66.8
47.5°	49.9
50°	36.3
52.5°	26.2
55°	19.4
57.5°	13.5
60°	7.6
62.5°	2.5
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)