

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224938

Luminaire Tested: **LSRWM2B05FL408050D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05FL408050D010 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 801.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224938

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224938

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	103	100	108	104	101	99		101	99	97			98	96	94			96
3	106	100	96	93	104	99	95	92		97	94	91			94	92	90			92
4	102	96	91	88	100	94	90	87		92	89	86			91	88	85			89
5	98	91	86	83	96	90	86	82		89	85	82			87	84	81			86
6	94	87	82	79	93	86	82	78		85	81	78			84	80	77			82
7	91	83	78	75	90	83	78	75		82	77	74			80	77	74			79
8	88	80	75	72	87	79	75	72		78	74	71			77	74	71			77
9	85	77	72	69	84	76	72	69		75	71	68			75	71	68			74
10	82	74	69	66	81	73	69	66		73	69	66			72	68	66			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	742968
5°	727415
10°	640642
15°	502626
20°	333762
25°	191598
30°	96073
35°	44354
40°	18052
45°	8053
50°	4218
55°	2634
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224938

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.9	21.3
10°-20°	339.2	42.4
20°-30°	210.8	26.3
30°-40°	63.6	7.9
40°-50°	13.0	1.6
50°-60°	3.4	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.9	90.0
0°-40°	784.5	97.9
0°-60°	800.8	100.0
0°-90°	801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1918	
5°	1871	171
15°	1253	339
25°	448	211
35°	94	64
45°	15	13
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224938

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1918.1
1°	1911.9
2°	1903.3
3°	1897.1
4°	1887.8
5°	1870.8
6°	1843.6
7°	1806.4
8°	1752.9
9°	1692.4
10°	1628.8
11°	1561.3
12°	1490.7
13°	1417.0
14°	1336.4
15°	1253.4
17.5°	1030.8
20°	809.7
22.5°	614.3
25°	448.3
27.5°	316.4
30°	214.8
32.5°	141.2
35°	93.8
37.5°	58.2
40°	35.7
42.5°	23.3
45°	14.7
47.5°	9.3
50°	7.0
52.5°	4.7
55°	3.9
57.5°	2.3
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224938

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)