

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225375

Luminaire Tested: **LSRWM2B05FL408050D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05FL408050D010 2LBDC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225375

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225375

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	96		98	96	94		96
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85
6	94	87	82	79	93	86	82	78	85	81	78		84	80	77		82
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79
8	87	80	75	72	86	79	75	71	78	74	71		77	74	71		76
9	84	77	72	69	83	76	72	68	75	71	68		74	71	68		74
10	82	74	69	66	81	73	69	66	73	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	720231
5°	707701
10°	631320
15°	499017
20°	332732
25°	193052
30°	96610
35°	45442
40°	17748
45°	7943
50°	3736
55°	2093
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225375

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	21.0
10°-20°	336.8	42.3
20°-30°	211.9	26.6
30°-40°	64.8	8.1
40°-50°	12.7	1.6
50°-60°	2.9	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.5	89.9
0°-40°	780.3	98.0
0°-60°	795.9	100.0
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1859	
5°	1820	167
15°	1244	337
25°	452	212
35°	96	65
45°	14	13
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225375

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1859.4
2.5°	1855.2
5°	1820.1
7.5°	1737.4
10°	1605.1
12.5°	1439.7
15°	1244.4
17.5°	1027.4
20°	807.2
22.5°	619.1
25°	451.7
27.5°	318.3
30°	216.0
32.5°	145.7
35°	96.1
37.5°	58.9
40°	35.1
42.5°	22.7
45°	14.5
47.5°	9.3
50°	6.2
52.5°	4.1
55°	3.1
57.5°	2.1
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)