

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224820

Luminaire Tested: **LSSQ2B10FL408040D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL408040D010 2LBDL*B
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 995.3 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224820

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224820

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85
6	94	87	82	79	93	86	82	78	85	81	78		84	80	77		82
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79
8	87	80	75	72	86	79	75	71	78	74	71		77	74	71		76
9	84	77	72	69	83	76	72	68	75	71	68		74	71	68		74
10	82	74	69	66	81	73	69	66	73	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	900541
5°	884889
10°	789396
15°	623972
20°	416038
25°	241347
30°	120807
35°	56838
40°	22198
45°	9915
50°	4700
55°	2634
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224820

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.6	21.0
10°-20°	421.2	42.3
20°-30°	264.9	26.6
30°-40°	81.0	8.1
40°-50°	15.9	1.6
50°-60°	3.6	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.7	89.9
0°-40°	975.7	98.0
0°-60°	995.2	100.0
0°-90°	995.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	995.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2325	
5°	2276	209
15°	1556	421
25°	565	265
35°	120	81
45°	18	16
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224820

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2324.9
2.5°	2319.7
5°	2275.8
7.5°	2172.4
10°	2007.0
12.5°	1800.2
15°	1556.0
17.5°	1284.6
20°	1009.3
22.5°	774.1
25°	564.7
27.5°	398.0
30°	270.1
32.5°	182.2
35°	120.2
37.5°	73.7
40°	43.9
42.5°	28.4
45°	18.1
47.5°	11.6
50°	7.8
52.5°	5.2
55°	3.9
57.5°	2.6
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)