

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224646

Luminaire Tested: **LSSQWM2B05FL408050D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224646
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408050D010 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 744.1 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224646

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224646

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	673556
5°	661276
10°	587858
15°	462325
20°	307629
25°	176597
30°	89230
35°	41990
40°	16889
45°	8381
50°	4580
55°	3242
60°	2944
65°	1741
70°	2152
75°	1497
80°	2231
85°	0



TEST NUMBER: P224646

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	20.9
10°-20°	312.3	42.0
20°-30°	194.3	26.1
30°-40°	59.7	8.0
40°-50°	13.1	1.8
50°-60°	4.7	0.6
60°-70°	2.4	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.3	89.0
0°-40°	722.1	97.0
0°-60°	739.9	99.4
0°-90°	744.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	744.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1739	
5°	1701	156
15°	1153	312
25°	413	194
35°	89	60
45°	15	13
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224646

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1738.9
2.5°	1731.3
5°	1700.7
7.5°	1623.4
10°	1494.6
12.5°	1340.0
15°	1152.9
17.5°	948.7
20°	746.3
22.5°	565.9
25°	413.2
27.5°	291.1
30°	199.5
32.5°	134.6
35°	88.8
37.5°	53.4
40°	33.4
42.5°	22.9
45°	15.3
47.5°	10.5
50°	7.6
52.5°	6.7
55°	4.8
57.5°	3.8
60°	3.8
62.5°	2.9
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)