

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224447

Luminaire Tested: **LSSQWM2B10FL408040D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL408040D010 2LBDL*WH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1035.1 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224447

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224447

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100	108	104	101	98		101	98	96			98	96	94			91
3	106	100	96	93	104	99	95	92		96	93	91			94	91	89			87
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			82
5	98	91	86	82	96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78	93	86	81	78		85	80	77			83	80	77			75
7	91	83	78	75	89	82	78	74		81	77	74			80	76	74			72
8	87	79	75	71	86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68	83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65	80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	955040
5°	918912
10°	808826
15°	635320
20°	431950
25°	252245
30°	128456
35°	60763
40°	26546
45°	11504
50°	5544
55°	3512
60°	2014
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224447

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.8	20.9
10°-20°	430.8	41.6
20°-30°	276.5	26.7
30°-40°	87.7	8.5
40°-50°	18.7	1.8
50°-60°	4.8	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	923.2	89.2
0°-40°	1010.9	97.7
0°-60°	1034.4	99.9
0°-90°	1035.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2466	
5°	2363	216
15°	1584	431
25°	590	277
35°	128	88
45°	21	19
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224447

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2465.6
2.5°	2442.0
5°	2363.3
7.5°	2234.8
10°	2056.4
12.5°	1838.7
15°	1584.3
17.5°	1312.8
20°	1047.9
22.5°	800.0
25°	590.2
27.5°	421.0
30°	287.2
32.5°	192.8
35°	128.5
37.5°	85.2
40°	52.5
42.5°	32.8
45°	21.0
47.5°	14.4
50°	9.2
52.5°	6.6
55°	5.2
57.5°	3.9
60°	2.6
62.5°	1.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)