

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223314

Luminaire Tested: **LD2B10D010 EU2B10NFL258035 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 984.6 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223314

CATALOG NUMBER: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223314

CATALOG NUMBER: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	104	102	104	102	100		101	99	98		98
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		96
4	106	101	97	95	104	100	97	94	98	95	93		96	94	92		95
5	103	98	94	91	102	97	94	91	95	92	90		94	91	89		93
6	101	95	91	89	99	94	91	88	93	90	88		92	89	87		91
7	98	92	89	86	97	92	88	86	91	88	85		90	87	85		89
8	96	90	86	84	95	90	86	84	89	86	83		88	85	83		87
9	94	88	84	82	93	88	84	82	87	84	82		86	83	81		85
10	92	86	82	80	91	86	82	80	85	82	80		84	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2262604
5°	2089082
10°	1414030
15°	481092
20°	176712
25°	93684
30°	48171
35°	22461
40°	7332
45°	3725
50°	1748
55°	675
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223314

CATALOG NUMBER: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	457.0	46.4
10°-20°	384.3	39.0
20°-30°	105.5	10.7
30°-40°	30.7	3.1
40°-50°	5.7	0.6
50°-60°	1.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	946.8	96.2
0°-40°	977.5	99.3
0°-60°	984.5	100.0
0°-90°	984.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5841	
5°	5373	457
15°	1200	384
25°	219	105
35°	48	31
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223314

CATALOG NUMBER: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5841.3
1°	5807.3
2°	5747.2
3°	5660.9
4°	5542.6
5°	5372.8
6°	5141.0
7°	4851.1
8°	4497.1
9°	4079.1
10°	3595.1
11°	3064.6
12°	2512.8
13°	1986.2
14°	1537.2
15°	1199.7
17.5°	676.9
20°	428.7
22.5°	305.5
25°	219.2
27.5°	155.2
30°	107.7
32.5°	75.6
35°	47.5
37.5°	19.4
40°	14.5
42.5°	10.7
45°	6.8
47.5°	3.9
50°	2.9
52.5°	1.9
55°	1.0
57.5°	1.0
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223314

CATALOG NUMBER: LD2B10D010 EU2B10NFL258035 2LBDSQC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)