

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224626

Luminaire Tested: **LSSQWM2B10FL408040D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL408040D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 998.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224626

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224626

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			79
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			76
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			72
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			69
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			67
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	908443
5°	890994
10°	791481
15°	624613
20°	416574
25°	239765
30°	121433
35°	56933
40°	23310
45°	10518
50°	5423
55°	3444
60°	2014
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224626

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.7	21.0
10°-20°	420.9	42.2
20°-30°	263.6	26.4
30°-40°	81.6	8.2
40°-50°	16.9	1.7
50°-60°	4.7	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.2	89.6
0°-40°	975.8	97.8
0°-60°	997.4	99.9
0°-90°	998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2345	
5°	2292	210
15°	1558	421
25°	561	264
35°	120	82
45°	19	17
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224626

CATALOG NUMBER: LSSQWM2B10FL408040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2345.3
2.5°	2333.8
5°	2291.5
7.5°	2183.9
10°	2012.3
12.5°	1800.9
15°	1557.6
17.5°	1277.0
20°	1010.6
22.5°	768.5
25°	561.0
27.5°	394.5
30°	271.5
32.5°	181.9
35°	120.4
37.5°	75.6
40°	46.1
42.5°	29.5
45°	19.2
47.5°	12.8
50°	9.0
52.5°	6.4
55°	5.1
57.5°	3.8
60°	2.6
62.5°	1.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)